

**TOSHIBA**  
Leading Innovation >>>

# 24SL410U

## Live for TV? You'll love this LED.

Our 24" class SL410U HDTV offers excellent picture quality and affordability too.



Step up to LED—and raise your expectations, too—by bringing home Toshiba's 24" class SL410U LED HDTV. Infused with legendary Toshiba quality and reliability, this versatile television dishes out excellent sound and imagery in clear 1080p full HD resolution. Featuring a sleek ultraslim profile, the SL410U looks just as great on a pedestal as it does in a kitchen, bedroom or kids' room. Plus, its convenient PC input makes it easy to show off your latest home movies, or plug it in as a bigscreen monitor. So get the LED quality you want at an LCD price you can afford, with Toshiba's model SL410U HDTV.

### Key Features:



#### 1080p Resolution<sup>1</sup>

See colors and details like you never have before! Enjoy the highest level of HD picture quality with 1080p Full HD.



#### DynaLight™

Increase detail and depth of the images on your screen with Dynalight™, a technology that monitors the brightness level of each video frame, even in low light settings.



#### USB Connection

Easily connect to your favorite tunes and photos, create slideshows, or listen to your personal playlists with this feature.



#### 2 HDMI®-CEC<sup>2</sup>

Easily connect to high-definition video, and amazingly immersive surround sound in one cable.

# Toshiba 24SL410U

## Cabinet

- Screen Size Class: 24 in.
- Actual Screen Size Diagonal: 23.5 in.

## Panel Specifications

- Backlighting System: LED
- Resolution: 1080p
- Frame Rate: 60Hz
- Backlighting Control: DynaLight™

## Video Chassis

- Native Mode™: Easily take control with Native Mode™! This technology displays the image edges normally lost to over-scanning.
- Gaming Mode: Initiate the gaming experience by reducing game controller delay with Gaming Mode.

## Audio

- Invisible Speaker System Design
- Speaker: 3W + 3W
- Mute/Half Mute

## Convenience

- Input Labeling
- Channel Browser
- Sleep Timer
- Remote Control

## Jack Pack


- HDMI® Digital Inputs<sup>2</sup>: 2 w/CEC  
Easily connect to high-definition video, and amazingly immersive surround sound in one cable.
- ColorStream Component  
Video Inputs: 1
- PC Input: 1
- USB Ports: 1 (Music/Photo)
- Composite: 1

## Product and Packaging

- VESA Mounting Pattern<sup>3</sup>:  
100mm × 100mm
- Limited Warranty: 1 Year  
Parts & Labor
- Energy Star Compliant
- Dimensions w/ Stand (W×H×D):  
22.98 in. × 16.31 in. × 8.68 in.  
Weight: 8.55 lbs.
- Dimensions w/o Stand (W×H×D):  
22.98 in. × 14.57 in. × 1.85 in.  
Weight: 9.64 lbs.
- Shipping Dimensions (W×H×D):  
25.71 in. × 18.70 in. × 4.96 in.  
Weight: 12.13 lbs.

## UPC

022265004234



**TOSHIBA**  
Leading Innovation >>>



<sup>1</sup>While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are all subject to change without notice.

<sup>2</sup>HDMI®-CEC Use of HDMI®-CEC requires an HDMI®-CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI®-CEC functions may not work even if your display/peripheral device is HDMI®-CEC compatible.

<sup>3</sup>VESA® Mounting Pattern If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.