

32L4200U

LED HDTV

TOSHIBA
Leading Innovation >>>

**FULL HD TV
THAT FITS YOU,
YOUR HOME,
YOUR BUDGET**



Thin LED with New Aero™ Design

Thin depth with LED quality for your office, den, bedroom, or family room. The new Aero™ design matches the thin bezel, and the stylish silver Aero™ wing to create a TV that looks great in any home décor.

New Dynamic Picture Mode

Creates pictures that seem to pop off the screen. The new Dynamic Mode enhances color, sharpness, brightness and contrast to provide incredible picture quality.

New Audyssey® Audio Technology

Audyssey Premium Television is a suite of advanced audio technologies that helps produce clear, rich and natural sound. For the L4200 series the suite includes:

- Audyssey EQ®
- Audyssey ABX™ (Bass Extension)
- Audyssey Dynamic Volume®

Multiple HD Inputs

Full connectivity with two HDMI®2 HD Inputs and an HD PC Input, so the TV can also be used as a large PC monitor. (Great for PC gaming!)



Say goodbye to standard-def with 720p HD resolution



Easily connect your PC to your TV for the big screen HD experience.



Dynamic backlight control for deeper blacks and more detail.



A sleeker, cleaner look that really stands out.



Easily connect to high-definition video and amazingly immersive surround sound in one cable.



Easily connect to your favorite tunes and photos, create slideshows, or listen to your personal playlists with this feature.

32L4200U

SPECIFICATIONS¹

TOSHIBA
Leading Innovation >>>

Screen Size: 32"

- Diagonal Screen Size: 31.5"
- Design: Aero™ Cosmetic Design

Panel

- Panel Type: LED
- Resolution: 720P HD
- Refresh Rate: 60Hz
- Backlight Control: DynaLight®

Video Chassis

- Dynamic Picture Mode
- Native Mode™
- Game Mode

Convenience

- Standard Remote Control

Audio

- Audyssey Premium Television™
 - Audyssey EQ®
 - Audyssey ABX™
 - Audyssey Dynamic Volume®
- Speaker Output: 14W

Connectivity

- HDMI® with CEC²: 2
- USB Media: 1
- High Definition PC Input: 1
- 3.5mm PC Audio Out: 1
- Digital Audio Out: 1
- ColorStream® Component Video: 1
- Composite: 1

Product and Packaging

- VESA Mounting Pattern³: 200mm x 100mm
- Limited Warranty: 1 Year Parts & Labor
- Power Consumption (On): 46W
- Power Consumption (Stand-by): 0.4W

- Product Dimensions & Weights
 - With Stand
 - Dimensions: 29.33"x19.88"x7.08"
 - Weight: 17.6 lbs.
 - Without Stand
 - Dimensions: 29.33"x18.58"x1.77"
 - Weight: 16.3 lbs
 - In Packaging
 - Dimensions: 33.62"x22.99"x4.80"
 - Weight: 24.3 lbs
- ENERGY STAR® 5.3 Compliant


What's in the box

- Remote Control (CT-90325)
- Batteries (AA x 2)
- Resource Guide
- Quick Start Guide
- Warranty


UPC Code: 022265054406

Country of Origin: China

Remote Control (CT-90325)



Related Products



Single DVD Player



Wi-Fi® Ready Blu-ray Disc™ Player



Wi-Fi® Built-in Blu-ray Disc™ Player

1. While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. 2. Use of HDMI® w/ CEC requires an HDMI® w/ CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI® w/ CEC functions may not work even if your display/peripheral device is HDMI® w/ CEC compatible. 3. If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.

© 2012 Toshiba America Information Systems, Inc. Aero, ColorStream, DynaLight and Native Mode are registered trademarks or trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. All other trademarks are the property of their respective owners. All rights reserved.