

# 24L4200U

LED HDTV

**TOSHIBA**  
Leading Innovation >>>

**FULL HD TV  
THAT FITS YOU,  
YOUR HOME,  
YOUR BUDGET**



#### **Thin LED with New Aero™ Design that Fits Anywhere**

Thin depth with LED quality for your kitchen, office or den. The new Aero™ design matches the thin bezel and the stylish silver Aero™ wing to create a TV that looks great in any home décor.

#### **1080p Full HD for Sharper Images**

Step up to 1080p Full HD<sup>2</sup> with more pixel resolution than standard HD for incredible image clarity to TV and your PC.

#### **New Dynamic Picture Mode**

Creates pictures that seem to pop off the screen. The new Dynamic Mode enhances color, sharpness, brightness and contrast to provide incredible picture quality.

#### **New Audyssey® Audio Technology**

Audyssey Premium Television is a suite of advanced audio technologies that helps produce clear, rich and natural sound. For the L4200 series the suite includes:

- Audyssey EQ®
- Audyssey ABX™ (Bass Extension)
- Audyssey Dynamic Volume®

#### **Multiple HD Inputs**

Full connectivity with two HDMI<sup>®3</sup> HD Inputs and an HD PC Input, so the TV can also be used as a large PC monitor. (Great for PC gaming!)

**1080P FULL HD**

Top HD picture quality with 1080p Full HD<sup>2</sup> resolution.

**PC HIGH DEFINITION INPUT**

Easily connect your PC to your TV for the big screen HD experience.

**DYNALIGHT**

Dynamic backlight control for deeper blacks and more detail.

**AERO DESIGN™**

A sleeker, cleaner look that really stands out.

**HDMI<sup>®</sup> X2**

Easily connect to high-definition video and amazingly immersive surround sound in one cable.

**USB MEDIA**

Easily connect to your favorite tunes and photos, create slideshows, or listen to your personal playlists with this feature.

# 24L4200U

## SPECIFICATIONS<sup>1</sup>

**TOSHIBA**  
Leading Innovation >>>

### Screen Size: 24"

- Diagonal Screen Size: 23.81"
- Design: Aero™ Cosmetic Design

### Panel

- Panel Type: LED
- Resolution: 1080P Full HD<sup>2</sup>
- Refresh Rate: 60Hz
- Backlight Control: DynaLight®

### Video Chassis

- Dynamic Picture Mode
- Native Mode™
- Game Mode

### Convenience

- Standard Remote Control

### Audio

- Audyssey Premium Television™
  - Audyssey EQ®
  - Audyssey ABX™
  - Audyssey Dynamic Volume®
- Speaker Output: 10W

### Connectivity

- HDMI® with CEC<sup>3</sup>: 2
- USB Media: 1
- High Definition PC Input: 1
- 3.5mm PC Audio Out: 1
- Digital Audio Out: 1
- ColorStream® Component Video: 1
- Composite: 1

### Product and Packaging

- VESA Mounting Pattern<sup>4</sup>: 100m x 100mm
- Limited Warranty: 1 Year Parts & Labor
- Power Consumption (On): 30W
- Power Consumption (Stand-by): 0.4W

### Product Dimensions & Weights

- With Stand
  - Dimensions: 22.36"x15.59"x7.00"
  - Weight: 9.9 lbs.
- Without Stand
  - Dimensions: 22.36"x14.29"x1.69"
  - Weight: 8.8 lbs.
- In Packaging
  - Dimensions: 25.66"x18.70"x5.11"
  - Weight: 15.4 lbs.
- ENERGY STAR® 5.3 Compliant


### What's in the box

- Remote Control (CT-90325)
- Batteries (AA x 2)
- Resource Guide
- Quick Start Guide
- Warranty

UPC Code: 022265054208

Country of Origin: China

### Remote Control (CT-90325)



### Related Products



Single DVD Player



Wi-Fi® Ready Blu-ray Disc™ Player



Wi-Fi® Built-in Blu-ray Disc™ Player

1. While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. 2. 1080p/24 fps encoded content and an HD display capable of accepting a 1080p/24Hz signal required for viewing 1080p/24 fps content. 3. Use of HDMI® w/ CEC requires an HDMI® w/ CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI® w/ CEC functions may not work even if your display/peripheral device is HDMI® w/ CEC compatible. 4. If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.